



HSB112FR100, Heat Shrink Tubing PVC, Thin, FR, Black

By Burndy
Catalog # [HSB112FR100](#)



1.50" ID Min (Expanded), .75" ID Max (Recovered), 250-500 Flex, PVC, Thin Wall, Flame Retardant, 100-Foot Reel

Features

- Heat Shrink Tubing, 1.50" ID Min (Exp), 0.75" ID Max (Rec)
- 250-500 Flex, PVC, Think Wall
- Flame Retardant, Black
- 600V, 100 Foot Reel

Specifications

Certification - CSA Approved	Yes
UL Listed	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	

Conductor

Conductor Range	250-500 Kcmil
Conductor Size	350kcmil - 750kcmil

Configuration

Connector Type	THIN WALL TUBES/REELS
----------------	-----------------------

Dimensions

Width	1.5 in
Height	1.5 in
Length	1200 in
Dimensions	1200 in x 1.5 in x 1.5 in

General

Material	Polyvinyl chloride
UPC	781810265772

Logistics

Minimum Pack Quantity	2
Carton Quantity	1
Pallet Quantity	1

Product Assets

[Catalog \[English\]](#)