



HSB116T300PF, Heat Shrink Tubing, Thin, Flame Rtrdnt, Black

By Burndy
Catalog # [HSB116T300PF](#)

.06" ID Min (Expanded), .03" Max (Recovered), #18 AWG, Black, 25-Foot Reel

Features

- Thin Wall Cross-Linked Black Polyolefin Heat Shrink Tubing
- #18 AWG, 600V
- Flame Retardant

Application

For Terminations And Splices

Specifications

Buy American Compliant	No
EU RoHS Indicator	Yes
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	Yes
UL Listed	No

Conductor

Conductor Size	18AWG
----------------	-------

Configuration

Connector Type	THIN WALL REEL
----------------	----------------

Dimensions

Package Length	7 in
Package Width	6 in
Package Weight	1.87 lb.
Package Height	7 in
Length	1200 in
Width	0.062 in
Height	0.062 in
Dimensions	1200 in x 0.062 in x 0.062 in

General

Sub Brand	HEAT SHRINK
Type	HS-T-PF, Thin Wall, Flexible, Flame Retardant
Material	Cross-linked Polyolefin
UPC	781810213100

Logistics

Minimum Pack Quantity	1
Carton Quantity	1
Pallet Quantity	1

Product Assets

[Catalog \[English\]](#)