



HSB116T48PF, Heat Shrink Tubing, Thin, Flame Rtrdnt, Black

By Burndy
Catalog # [HSB116T48PF](#)

.06" ID Min (Expanded), .03" Max (Recovered), #18 AWG, Black, 4-Foot Reel

Features

- Thin Wall Cross-Linked Black Polyolefin Heat Shrink Tubing
- #18 AWG, 600 V

Application

For Terminations And Splices

Specifications

Buy American Compliant	No
EU RoHS Indicator	Yes
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	Yes
UL Listed	No

Configuration

Connector Type	THIN WALL REEL
----------------	----------------

Dimensions

Package Length	6 in
Package Width	1 in
Package Weight	0.54 lb.
Package Height	10 in
Length	48 in
Width	0.062 in
Height	0.062 in
Dimensions	48 in x 0.062 in x 0.062 in

General

Sub Brand	HEAT SHRINK
Type	HS-T-PF, Thin Wall, Flexible, Flame Retardant
Material	Cross-linked Polyolefin
UPC	781810212226

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalog \[English\]](#)