



HSB116T6PF26, Heat Shrink Tubing, Thin Wall, Black

By Burndy
Catalog # [HSB116T6PF26](#)



.06" ID Min (Expanded), .03" Max (Recovered), #18 AWG, Black, 6-Inch Lengths

Features

- Thin Wall Cross-Linked Polyolefin Heat Shrink Tubing
- #18 AWG, 600 V, 6" Long
- Flame Retardant, All Black

Application

For Terminations And Splices

Specifications

Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
EU RoHS Indicator	Yes
Buy America(n) Qualified	Contact Manufacturer
UL Listed	No
Certification - CSA Approved	Yes

Dimensions

Package Height	10 in
Length	6 in

Package Weight	0.58 lb.
Package Length	6 in
Package Width	1 in
Height	0.062 in
Width	0.062 in
Dimensions	6 in x 0.062 in x 0.062 in

General

Sub Brand	HEAT SHRINK
UPC	781810214404
Type	HS-T-PF, Thin Wall, Flexible, Flame Retardant
Material	Polyolefin

Logistics

Minimum Pack Quantity	1
Number of Pieces in Package	26
Carton Quantity	260

Product Assets

[Catalog \[English\]](#)