



HSB12FR, Heat Shrink Tubing PVC, Thin Wall, FR, Black

By Burndy
Catalog # [HSB12FR](#)

.5" ID Min (Expanded), .25" Max (Recovered), Flame Retardant, Black, 50-Foot Reel



Features

- Flame Retardant
- Flexible Polyvinylchloride
- 2:1 Shrink Ratio
- 600 Volts

Application

For Terminations And Splices

Specifications

Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Buy American Compliant	No
UL Listed	No
Certification - CSA Approved	Yes

Conductor

Conductor Size	4AWG - 1AWG
Conductor Range	#6 AWG to #4 AWG

Configuration

Connector Type	THIN WALL TUBES/REELS
----------------	-----------------------

Current

Voltage Rating	600 V
----------------	-------

Dimensions

Length	600 in
Thickness	0.03
Height	0.5 in
Width	0.5 in
Dimensions	600 in x 0.5 in x 0.5 in

General

Sub Brand	HEAT SHRINK
Product Type	PVC Thin Wall Heat Shrink
UPC	781810265789
Type	HS-FR, Thin Wall, Flexible, Fire Retardant
Material	Polyvinyl chloride

Logistics

Minimum Pack Quantity	1
Pallet Quantity	360
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)