



HSB12FR250, Heat Shrink PVC, Thin Wall, Flame Rtrdnt, Black

By Burndy
Catalog # [HSB12FR250](#)

Thin wall heat shrink tubing



Features

- Heat Shrink Tubing, 0.50" ID Min (Exp), 0.25" ID Max (Rec)
- PVC, Fire Retardant
- Thin Wall Black
- 250 Foot Reel

Specifications

Certification - CSA Approved	Yes
UL Listed	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM

Conductor

Conductor Range	#6 AWG to #4 AWG
Conductor Size	4AWG - 1AWG

Configuration

Connector Type	THIN WALL TUBES/REELS
----------------	-----------------------

Dimensions

Width	0.5 in
Height	0.5 in
Length	3000 in
Dimensions	3000 in x 0.5 in x 0.5 in

General

Material	Polyvinyl chloride
UPC	781810265796

Logistics

Minimum Pack Quantity	2
Carton Quantity	1
Pallet Quantity	1

Product Assets

[Catalog \[English\]](#)