



HSB12T1200PF, Heat Shrink Tubing, Thin, Flame Rtrdnt, Black

By Burndy
Catalog # [HSB12T1200PF](#)

.5" ID Min (Expanded), .25" ID Max (Recovered), Flame Retardant, Black, 100-Foot Reel

Features

- Heat Shrink Tubing, 0.50" ID Min (Exp), 0.25" ID Max (Rec)
- Polyolefin, Thin Wall, Black
- Shrink Ratio 2:1, 600 V, 100 Foot Reel

Specifications

Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	Yes

Conductor

Conductor Range	#6 AWG to #2 AWG
-----------------	------------------

Dimensions

Height	0.5 in
Width	0.5 in
Length	1200 in
Dimensions	1200 in x 0.5 in x 0.5 in

General

UPC	781810242421
Material	Polyolefin

Logistics

Minimum Pack Quantity	2
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)