



HSB12T300PF, Heat Shrink Tubing, Thin Wall, Black

By Burndy
Catalog # [HSB12T300PF](#)

.5" ID Min (Expanded), .12" ID Max (Recovered), Flame Retardant, Black, 25-Foot Reel

Features

- Heat Shrink Tubing, 0.50" ID Min (Exp), 0.12" ID Max (Rec)
- 6-2 AWG, Cross Linked Polyolefin
- Thin Wall, Flame Retardant
- Black, 600 V

Application

For Terminations And Splices

Specifications

Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
EU RoHS Indicator	Yes
UL Listed	No
Certification - CSA Approved	Yes

Conductor

Conductor Size	6AWG - 2AWG
----------------	-------------

Conductor Range	#6 AWG to #2 AWG
-----------------	------------------

Configuration

Connector Type	THIN WALL REEL
----------------	----------------

Dimensions

Length	300 in
Height	0.5 in
Width	0.5 in
Dimensions	300 in x 0.5 in x 0.5 in

General

Sub Brand	HEAT SHRINK
UPC	781810213735
Type	HS-T-PF, Thin Wall, Flexible, Flame Retardant
Material	Cross-linked Polyolefin

Product Assets

[Catalog \[English\]](#)