



HSB12T48PF, Heat Shrink Tubing, Thin Wall, Black

By Burndy
Catalog # [HSB12T48PF](#)

.5" ID Min (Expanded), .25" ID Max (Recovered), Flame Retardant, Black, 4-Foot Reel

Features

- Heat Shrink Tubing, 0.50" ID Min (Exp), 0.25" ID Max (Rec)
- Polyolefin, Thin Wall, Black
- Shrink Ratio 2:1, 600 V
- 4 Foot Reel

Specifications

Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	Yes

Conductor

Conductor Size	6AWG - 2AWG
Conductor Range	#6 AWG to #2 AWG

Configuration

Connector Type	THIN WALL REEL
----------------	----------------

Dimensions

Height	0.5 in
Width	0.5 in
Length	48 in
Dimensions	48 in x 0.5 in x 0.5 in

General

UPC	781810212714
Material	Cross-linked Polyolefin

Product Assets

[Catalog \[English\]](#)