



HSB14FR, Heat Shrink Tubing PVC, Thin Wall, FR, Black

By Burndy
Catalog # [HSB14FR](#)



.25" ID Min (Expanded), .125" ID Max (Recovered), Flame Retardant, Black, 50-Foot Reel

Features

- Flame Retardant
- Flexible Polyvinylchloride
- 2:1 Shrink Ratio
- 600 Volts

Application

For Terminations And Splices

Specifications

Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
EU RoHS Indicator	Yes
UL Listed	No
Certification - CSA Approved	Yes

Conductor

Conductor Size	12AWG -8AWG
Conductor Range	#12 AWG to #10 AWG

Configuration

Connector Type	THIN WALL TUBES/REELS
----------------	-----------------------

Dimensions

Length	600 in
Height	0.25 in
Width	0.25 in
Dimensions	600 in x 0.25 in x 0.25 in

General

Sub Brand	HEAT SHRINK
UPC	781810265819
Type	HS-FR, Thin Wall, Flexible, Fire Retardant
Material	Polyvinyl chloride

Logistics

Minimum Pack Quantity	1
Pallet Quantity	128
Carton Quantity	16

Product Assets

[Catalog \[English\]](#)