



HSB14FR250, Heat Shrink PVC, Thin Wall, Flame Rtrdnt, Black

By Burndy
Catalog # [HSB14FR250](#)



.25" ID Min (Expanded), .125" ID Max (Recovered), Flame Retardant, Black, 250-Foot Reel

Features

- Heat Shrink Tubing, 0.25" ID (Exp), 0.13" ID Max (Rec)
- #12-#10, PVC, Fire Retardant
- Thin Wall, Black
- 250 Foot Reel

Specifications

Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	Yes

Conductor

Conductor Size	12AWG -8AWG
Conductor Range	#12 AWG to #10 AWG

Configuration

Connector Type	THIN WALL TUBES/REELS
----------------	-----------------------

Dimensions

Height	0.25 in
Width	0.25 in
Length	3000 in
Dimensions	3000 in x 0.25 in x 0.25 in

General

UPC	781810265826
Material	Polyvinyl chloride

Logistics

Minimum Pack Quantity	1
Pallet Quantity	360
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)