



HSB14FR250FT, Heat Shrink, Thin Wall, Flame Rtrdnt, Black

By Burndy
Catalog # [HSB14FR250FT](#)



.25" ID Min (Expanded), .125" ID Max (Recovered), Black, Flame Retardant, 250-Foot Reel

Features

- Heat Shrink Tubing, 0.25" ID Min (Exp), 0.13" ID Max (Rec)
- #12-#10, PVC, Fire Retardant
- Thin Wall, Black
- 250 Foot Reel

Specifications

Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	No
Certification - CSA Approved	Yes

Dimensions

Height	0.25 in
--------	---------

Width	0.25 in
Package Height	0.000 in
Length	3000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimensions	3000 in x 0.25 in x 0.25 in

General

UPC	781810038512
-----	--------------

Logistics

Minimum Pack Quantity	250
-----------------------	-----

Product Assets

[Catalog \[English\]](#)