



HSB14T1200PF, Heat Shrink Tubing, Thin, Flame Rtrdnt, Black

By Burndy
Catalog # [HSB14T1200PF](#)

.25" ID Min (Expanded), .125" ID Max (Recovered), Black, Flame Retardant, 100-Foot Reel

Features

- Heat Shrink Tubing, 0.25" ID Min (Exp), 0.12" ID Max (Rec)
- Polyolefin, Thin Wall, Black
- Shrink Ratio 2:1, 600 V
- 100 Foot Reel

Specifications

Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	Yes

Dimensions

Height	0.25 in
Width	0.25 in
Package Height	0.000 in

Length	1200 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimensions	1200 in x 0.25 in x 0.25 in

General

UPC	781810242469
Material	Polyolefin

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)