



HSB150H12PF3, Heat Shrink Tubing, Heavy Wall, Black

By Burndy
Catalog # [HSB150H12PF3](#)

1.5" ID Min (Expanded), .5" ID Max (Recovered), Thick Wall, Black, 12" Length, 3-Piece package, 1500V

Features

- Heat Shrink Tubing, 1.50" ID Min (Exp), 0.50" ID Max (Rec)
- 2/O - 350, Polyolefin, Thick Wall
- Black, Shrink Ratio 3:1, 1500 V
- UL486D Listed for Direct Burial

Specifications

Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor Size	2/OAWG - 350kcmil
Conductor Range	#2/O AWG - 350 Kcmil

Configuration

Connector Type	HEAVY WALL TUBES
----------------	------------------

Current

Voltage Rating	1500 V
----------------	--------

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in

General

UPC	781810214855
Material	Cross-linked Polyolefin

Logistics

Minimum Pack Quantity	1
Pallet Quantity	240
Carton Quantity	30

Product Assets

[Catalog \[English\]](#)