



HSB150T48PF, Heat Shrink Tubing, Thin, Flame Rtrdnt, Black

By Burndy
Catalog # [HSB150T48PF](#)

1.5" ID Min (Expanded), .75" ID Max (Recovered), Thin Wall, Black, 4-Foot Reel

Features

- Heat Shrink Tubing, 1.50" ID Min (Exp), 0.75" ID Max (Rec)
- 2/O - 350, Polyolefin, Thin Wall, Black
- Shrink Ratio 3:1, 600 V
- 4 Foot Reel

Specifications

Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	Yes

Conductor

Conductor Size	250kcmil - 500kcmil
Conductor Range	#2/O AWG - 350 Kcmil

Configuration

Connector Type	THIN WALL REEL
----------------	----------------

Dimensions

Height	1.5 in
Width	1.5 in
Length	48 in
Dimensions	48 in x 1.5 in x 1.5 in

General

UPC	781810212929
Material	Cross-linked Polyolefin

Product Assets

[Catalog \[English\]](#)