



HSB18FR250, Heat Shrink Tubing PVC, Thin, FR, Black

By Burndy
Catalog # [HSB18FR250](#)



0.125" ID Min (Expanded), .062" ID Max (Recovered), Flame Retardant, 250-Foot Reel

Features

- Heat Shrink Tubing, 0.13" ID Min (Exp), 0.06" ID Max (Rec)
- #16-#14, PVC, Fire Retardant
- Thin Wall, Black
- 250 Foot Reel

Specifications

Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	Yes

Conductor

Conductor Size	16AWG - 14AWG
Conductor Range	#16 AWG to #14 AWG

Configuration

Connector Type	THIN WALL TUBES/REELS
----------------	-----------------------

Dimensions

Package Height	0.000 in
Length	3000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Height	0.125 in
Width	0.125 in
Dimensions	3000 in x 0.125 in x 0.125 in

General

UPC	781810265888
Material	Polyvinyl chloride

Logistics

Minimum Pack Quantity	16
Pallet Quantity	576
Carton Quantity	16

Product Assets

[Catalog \[English\]](#)