



HSB18T1200PF, Heat Shrink Tubing, Thin, Flame Rtrdnt, Black

By Burndy
Catalog # [HSB18T1200PF](#)

0.125" ID Min (Expanded), .062" ID Max (Recovered), Flame Retardant, 100-Foot Reel

Features

- Heat Shrink Tubing, 0.12" ID Min (Exp), 0.06" ID Max (Rec)
- Polyolefin, Thin Wall, Black
- Shrink Ratio 2:1, 600 V
- 100 Foot Reel

Specifications

Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	No
Certification - CSA Approved	Yes

Conductor

Conductor Range	#18 AWG to #14 AWG
-----------------	--------------------

Dimensions

Height	0.125 in
Width	0.125 in
Length	1200 in
Dimensions	1200 in x 0.125 in x 0.125 in

General

UPC	781810242483
Material	Polyolefin

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)