



HSB18T300PF, Heat Shrink Tubing, Thin, Flame Rtrdnt, Black

By Burndy
Catalog # [HSB18T300PF](#)

0.125" ID Min (Expanded), .062" ID Max (Recovered), Flame Retardant, 25-Foot Reel

Features

- Heat Shrink Tubing, 0.12" ID Min (Exp), 0.06" ID Max (Rec)
- #18-#14 AWG, Cross Linked Polyolefin
- Thin Wall, Flame Retardant
- Black, 600 V

Application

For Terminations And Splices

Specifications

Buy American Compliant	No
EU RoHS Indicator	Yes
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	Yes
UL Listed	No

Conductor

Conductor Size	18AWG - 14AWG
Conductor Range	#18 AWG to #14 AWG

Configuration

Connector Type	THIN WALL REEL
----------------	----------------

Dimensions

Package Length	7 in
Package Width	6 in
Package Weight	2.2 lb.
Package Height	7 in
Length	300 in
Width	0.125 in
Height	0.125 in
Dimensions	300 in x 0.125 in x 0.125 in

General

Sub Brand	HEAT SHRINK
Type	HS-T-PF, Thin Wall, Flexible, Flame Retardant
Material	Cross-linked Polyolefin
UPC	781810213452

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalog \[English\]](#)