



HSB18T48PF, Heat Shrink Tubing, Thin, Flame Rtrdnt, Black

By Burndy
Catalog # [HSB18T48PF](#)

0.125" ID Min (Expanded), .062" ID Max (Recovered), Flame Retardant, 4-Foot Reel

Features

- Thin Wall Cross-Linked Black Polyolefin Heat Shrink Tubing
- #14-#18 AWG, 600 V
- Flame Retardant

Application

For Terminations And Splices

Specifications

Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
EU RoHS Indicator	Yes
UL Listed	No
Certification - CSA Approved	Yes

Conductor

Conductor Size	18AWG - 14AWG
Conductor Range	#18 AWG to #14 AWG

Configuration

Connector Type	THIN WALL REEL
----------------	----------------

Dimensions

Length	48 in
Height	0.125 in
Width	0.125 in
Dimensions	48 in x 0.125 in x 0.125 in

General

Sub Brand	HEAT SHRINK
UPC	781810212370
Type	HS-T-PF, Thin Wall, Flexible, Flame Retardant
Material	Cross-linked Polyolefin

Product Assets

[Catalog \[English\]](#)