



HSB200FR, Heat Shrink Tubing PVC, Thin, Flame Rtrdnt, Black

By Burndy
Catalog # [HSB200FR](#)



.2" ID Min (Expanded), 1" ID Max (Recovered), Flame Retardant, 25-Foot Reel

Features

- Flame Retardant
- Flexible Polyvinylchloride
- 2:1 Shrink Ratio
- 600 Volts

Specifications

Certification - CSA Approved	Yes
UL Listed	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM

Conductor

Conductor Range	500-750 Kcmil
Conductor Size	800kcmil - 1000kcmil

Configuration

Connector TypeTHIN WALL TUBES/REELS

Dimensions

Width	2 in
Height	2 in
Length	300 in
Dimensions	300 in x 2 in x 2 in

General

Material	Polyvinyl chloride
UPC	781810265895

Logistics

Minimum Pack Quantity1

Product Assets

[Catalog \[English\]](#)