



HSB200FR100, Heat Shrink Tubing PVC, Thin, FR, Black

By Burndy
Catalog # [HSB200FR100](#)



.2" ID Min (Expanded), 1" ID Max (Recovered), Flame Retardant, 100-Foot Reel

Features

- Heat Shrink Tubing, 2" ID Min (Exp), 1" ID Max (Rec)
- PVC, Thin Wall, Black
- 100 Foot Reel

Specifications

Certification - CSA Approved	Yes
UL Listed	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM

Conductor

Conductor Range	500-750 Kcmil
Conductor Size	800kcmil - 1000kcmil

Configuration

Connector Type	THIN WALL TUBES/REELS
----------------	-----------------------

Dimensions

Width	2 in
Height	2 in
Length	1200 in
Dimensions	1200 in x 2 in x 2 in

General

Material	Polyvinyl chloride
UPC	781810265925

Logistics

Minimum Pack Quantity	2
Carton Quantity	2
Pallet Quantity	72

Product Assets

[Catalog \[English\]](#)