



HSB316T48PF, Heat Shrink Tubing, Thin, Flame Rtrdnt, Black

By Burndy
Catalog # [HSB316T48PF](#)

.19" ID Min (Expanded), .09" ID Max (Recovered), Flame Retardant, Black, 4-Foot Reel

Features

- Thin Wall Cross-Linked Black Polyolefin Heat Shrink Tubing
- #12-#18 AWG, 600 V
- Flame Retardant

Application

For Terminations And Splices

Specifications

Buy American Compliant	No
EU RoHS Indicator	Yes
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	Yes
UL Listed	No

Conductor

Conductor Size	18AWG - 12AWG
----------------	---------------

Configuration

Connector Type	THIN WALL REEL
----------------	----------------

Dimensions

Package Length	6 in
Package Width	1 in
Package Weight	0.63 lb.
Package Height	10 in
Length	48 in
Width	0.187 in
Height	0.187 in
Dimensions	48 in x 0.187 in x 0.187 in

General

Sub Brand	HEAT SHRINK
Type	HS-T-PF, Thin Wall, Flexible, Flame Retardant
Material	Cross-linked Polyolefin
UPC	781810212462

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalog \[English\]](#)