



HSB316T6PF18, Heat Shrink Tubing, Thin, Flame Rtrdnt, Black

By Burndy
Catalog # [HSB316T6PF18](#)



.19" Min (Expanded), .09" ID Max (Recovered), Flame Retardant, Black, 6" Length, 18 Pieces per package

Features

- Thin Wall Cross-Linked Polyolefin Heat Shrink Tubing
- #12-#18 AWG, 600 V
- 6.00" Length
- Flame Retardant, All Black

Application

For Terminations And Splices

Specifications

Certification - ETL	No
Standards - RoHS Compliance Status	CM
EU RoHS Indicator	Yes
UL Listed	No
Certification - CSA Approved	Yes

Conductor

Conductor Range	#18 AWG to #12 AWG
-----------------	--------------------

Dimensions

Length	6 in
Height	0.187 in
Width	0.187 in
Dimensions	6 in x 0.187 in x 0.187 in

General

Sub Brand	HEAT SHRINK
UPC	781810214527
Type	HS-T-PF, Thin Wall, Flexible, Flame Retardant
Material	POLYOLEFIN

Logistics

Number of Pieces in Package	18
Carton Quantity	180

Product Assets

[Catalog \[English\]](#)