



HSB34FR, Heat Shrink Tubing PVC, Thin, Flame Rtrdnt, Black

By Burndy
Catalog # [HSB34FR](#)



.75" ID Min (Expanded), .0375" ID Max (Recovered), Thin Wall, PVC, Fire retardant, Black, 50-Foot Reel

Features

- Flame Retardant
- Flexible Polyvinylchloride
- 2:1 Shrink Ratio
- 600 Volts

Specifications

Certification - CSA Approved	Yes
UL Listed	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM

Conductor

Conductor Range	#2 AWG to # 1/0 AWG
Conductor Size	1/0AWG - 3/0AWG

Configuration

Connector Type	THIN WALL TUBES/REELS
----------------	-----------------------

Dimensions

Width	0.75 in
Height	0.75 in
Length	300 in
Dimensions	300 in x 0.75 in x 0.75 in

General

Material	Polyvinyl chloride
UPC	781810265932

Logistics

Minimum Pack Quantity	1
Carton Quantity	1
Pallet Quantity	50

Product Assets

[Catalog \[English\]](#)