



HSB34FR250, Heat Shrink Tubing PVC, Thin, FR, Black

By Burndy
Catalog # [HSB34FR250](#)



.75" ID Min (Expanded), .0375" ID Max (Recovered), Thin Wall, PVC, Fire retardant, Black, 250-Foot Reel

Features

- Heat Shrink Tubing, 0.75" ID Min (Exp), 0.375" ID Max (Rec)
- #2-1/0, PVC, Fire Retardant
- Thin Wall, Black
- 250 Foot Reel

Specifications

Certification - CSA Approved	Yes
UL Listed	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	

Conductor

Conductor Range	#2 AWG to # 1/0 AWG
Conductor Size	1/0AWG - 3/0AWG

Configuration

Connector Type	THIN WALL TUBES/REELS
----------------	-----------------------

Dimensions

Width	0.75 in
Height	0.75 in
Length	3000 in
Dimensions	3000 in x 0.75 in x 0.75 in

General

Material	Polyvinyl chloride
UPC	781810265949

Logistics

Minimum Pack Quantity	2
Carton Quantity	10
Pallet Quantity	360

Product Assets

[Catalog \[English\]](#)