



HSB34FR250FT, Heat Shrink Tubing, Thin, Flame Rtrdnt, Black

By Burndy
Catalog # [HSB34FR250FT](#)



.75" ID Min (Expanded), .0375" ID Max (Recovered), Black, Thin Wall, PVC, Fire retardant, 250-Foot Reel

Features

- Heat Shrink Tubing, 0.75" ID Min (Exp), 0.375" ID Max (Rec)
- #2 - 1/0, PVC, Fire Retardant
- Thin Wall, Black
- 250 Foot Reel

Specifications

Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	Yes

Current

Voltage Rating	600 V
----------------	-------

Dimensions

Height	0.75 in
Width	0.75 in
Package Height	0.000 in
Length	3000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimensions	3000 in x 0.75 in x 0.75 in

General

Product Type	PVC Thin Wall Heat Shrink
UPC	781810038543

Logistics

Minimum Pack Quantity	250
-----------------------	-----

Product Assets

[Catalog \[English\]](#)