



HSB34H6PF10, Heat Shrink Tubing, Heavy Wall, Black

By Burndy
Catalog # [HSB34H6PF10](#)

.75" ID Min (Expanded), .24" ID Max (Recovered), Black, Thick Wall, 6" Lengths, 10 Pieces per package

Features

- Heat Shrink Tubing, 0.75" ID Min (Exp), 0.22" ID Max (Rec)
- #6-#2, Polyolefin, Thick Wall, Black
- Shrink Ratio 3:1, 1500 V
- UL486D Listed for Direct Burial

Specifications

Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor Size	6AWG - 2AWG
Conductor Range	#6 AWG to #2 AWG

Configuration

Connector Type	HEAVY WALL TUBES
----------------	------------------

Current

Voltage Rating	1500 V
----------------	--------

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in

General

UPC	781810214800
Material	Cross-linked Polyolefin

Logistics

Minimum Pack Quantity	1
Pallet Quantity	300
Carton Quantity	250

Product Assets

[Catalog \[English\]](#)