



HSB34T1200PF, Heat Shrink Tubing, Thin, Flame Rtrdnt, Black

By Burndy  
Catalog # [HSB34T1200PF](#)

.75" ID Min (Expanded), .0375" ID Max (Recovered), Black, Thin Wall, Fire retardant, 100-Foot Reel

Features

- Heat Shrink Tubing, 0.75" ID Min (Exp), 0.38" ID Max (Rec)
- Polyolefin, Thin Wall, Black
- Shrink Ratio 2:1, 600 Volt
- 100 Foot Reel

Specifications

|                                    |     |
|------------------------------------|-----|
| Certification - ETL                | No  |
| Standards - RoHS Compliance Status | CM  |
| UL Listed                          | No  |
| Certification - CSA Approved       | Yes |

Dimensions

|        |         |
|--------|---------|
| Height | 0.75 in |
|--------|---------|

|            |                             |
|------------|-----------------------------|
| Width      | 0.75 in                     |
| Length     | 1200 in                     |
| Dimensions | 1200 in x 0.75 in x 0.75 in |

General

|          |              |
|----------|--------------|
| UPC      | 781810242407 |
| Material | Polyolefin   |

Logistics

|                       |   |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
| Pallet Quantity       | 1 |
| Carton Quantity       | 1 |

Product Assets

[Catalog \[English\]](#)