



HSB34T300PF, Heat Shrink Tubing, Thin, Flame Rtrdnt, Black

By Burndy
Catalog # [HSB34T300PF](#)

.75" ID Min (Expanded), .0375" ID Max (Recovered), Black, Thin Wall, Fire retardant, 25-Foot Reel

Features

- Heat Shrink Tubing, 0.75" ID Min (Exp), 0.375" ID Max (Rec)
- Polyolefin, Thin Wall, Black
- Shrink Ratio 2:1, 600 V
- 25 Foot Reel

Specifications

Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	Yes

Conductor

Conductor Size	1AWG - 3/0AWG
Conductor Range	#1 AWG to #3/0 AWG

Configuration

Connector Type	THIN WALL REEL
----------------	----------------

Dimensions

Height	0.75 in
Width	0.75 in
Package Height	0.000 in
Length	300 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimensions	300 in x 0.75 in x 0.75 in

General

UPC	781810213865
Material	Cross-linked Polyolefin

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalog \[English\]](#)