



# HSB34T48PF, Heat Shrink Tubing, Thin, Flame Rtrdnt, Black

By Burndy  
Catalog # [HSB34T48PF](#)

.75" ID Min (Expanded), .0375" ID Max (Recovered), Black, Thin Wall, Fire retardant, 4-Foot Reel

## Features

- Heat Shrink Tubing, 0.75" ID Min (Exp), 0.375" ID Max (Rec)
- Polyolefin, Thin Wall, Black
- Shrink Ratio 2:1, 600 V
- 4 Foot Reel

## Specifications

|                              |     |
|------------------------------|-----|
| Certification - ETL          | No  |
| Standards - RoHS Compliance  | CM  |
| Status                       |     |
| UL Listed                    | No  |
| Certification - CSA Approved | Yes |

## Conductor

|                 |                    |
|-----------------|--------------------|
| Conductor Size  | 1AWG - 3/0AWG      |
| Conductor Range | #1 AWG to #3/0 AWG |

## Configuration

|                |                |
|----------------|----------------|
| Connector Type | THIN WALL REEL |
|----------------|----------------|

## Dimensions

|                |                           |
|----------------|---------------------------|
| Height         | 0.75 in                   |
| Width          | 0.75 in                   |
| Package Height | 0.000 in                  |
| Length         | 48 in                     |
| Package Weight | 0.000 lb.                 |
| Package Length | 0.000 in                  |
| Package Width  | 0.000 in                  |
| Dimensions     | 48 in x 0.75 in x 0.75 in |

## General

|          |                         |
|----------|-------------------------|
| UPC      | 781810212783            |
| Material | Cross-linked Polyolefin |

## Logistics

|                       |   |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

## Product Assets

[Catalog \[English\]](#)