



HSB34T6PF8, Heat Shrink Tubing, Thin, Flame Rtrdnt, Black

By Burndy
Catalog # [HSB34T6PF8](#)



.75" ID Min (Expanded), .0375" ID Max (Recovered), Black, Thin Wall, Fire retardant, 6" Length, 8 Pieces per package

Features

- Heat Shrink Tubing, 0.75" ID Min (Exp), 0.375" ID Max (Rec)
- Polyolefin, Thin Wall, Black
- Shrink Ratio 2:1, 600 V
- 4 Foot Reel

Specifications

Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	Yes

Conductor

Conductor Range	#1 AWG to #3/0 AWG
-----------------	--------------------

Dimensions

Height	0.75 in
--------	---------

Width	0.75 in
Package Height	0.000 in
Length	6 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimensions	6 in x 0.75 in x 0.75 in

General

UPC	781810214565
Material	Polyolefin

Logistics

Minimum Pack Quantity	1
Carton Quantity	80

Product Assets

[Catalog \[English\]](#)