



HSB35H3PF25, Heat Shrink Tubing, Thin, Flame Rtrdnt, Black

By Burndy
Catalog # [HSB35H3PF25](#)

.35" ID Min (Expanded), .15" ID Max (Recovered), Black, Thick Wall, Flame Retardant, 3" Length, 25 Pieces per package

Features

- Heavy Wall Heat Shrink Tubing
- Shrink Ratio 3:1
- Inside diameter is coated with adhesive sealant to protect against moisture and corrosion
- 1500V
- UL486D Listed for Direct Burial

Application

For Direct Burial

Specifications

Certification - ETL	No
Standards - RoHS Compliance Status	CM
Buy American Compliant	No
EU RoHS Indicator	Yes
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor Size	14AWG - 10AWG
Conductor Range	#14 AWG to #10 AWG

Configuration

Connector Type	HEAVY WALL TUBES
----------------	------------------

Current

Voltage Rating	1500 V
----------------	--------

Dimensions

Package Height	10 in
Package Weight	4.7 lb.
Package Length	6 in
Package Width	1 in

General

Sub Brand	HEAT SHRINK
UPC	781810214763
Type	HS-H-PF, Heavy Wall, Flame Retardant
Material	Cross-linked Polyolefin

Logistics

Minimum Pack Quantity	1
Pallet Quantity	22500
Carton Quantity	625

Product Assets

[Catalog \[English\]](#)