



HSB38FR, Heat Shrink Tubing PVC, Thin Wall, FR, Black

By Burndy
Catalog # [HSB38FR](#)



.38" ID Min (Expanded), .19" ID Max (Recovered), Black, Fire Retardant, Thin Wall, 50-Foot Reel

Features

- Flame Retardant
- Flexible Polyvinylchloride
- 2:1 Shrink Ratio
- 600 Volts

Specifications

Certification - ETL	No
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	Yes
UL Listed	No

Conductor

Conductor Size	6AWG - 4AWG
Conductor Range	#8 AWG to #6 AWG

Configuration

Connector Type	THIN WALL TUBES/REELS
----------------	-----------------------

Dimensions

Length	300 in
Width	0.375 in
Height	0.375 in
Dimensions	300 in x 0.375 in x 0.375 in

General

Material	Polyvinyl chloride
UPC	781810265956

Logistics

Minimum Pack Quantity	1
Carton Quantity	16
Pallet Quantity	128

Product Assets

[Catalog \[English\]](#)