



HSB38FR250, Heat Shrink Tubing PVC, Thin, FR, Black

By Burndy
Catalog # [HSB38FR250](#)



.38" ID Min (Expanded), .19" ID Max (Recovered), Black, Fire Retardant, Thin Wall, 250-Foot Reel

Features

- Heat Shrink Tubing, 0.38" ID Min (Exp), 0.19" ID Max (Rec)
- #8-#6, PVC, Fire Retardant
- Thin Wall, Black
- 250 Foot Reel

Specifications

Certification - CSA Approved	Yes
UL Listed	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	

Conductor

Conductor Range	#8 AWG to #6 AWG
Conductor Size	6AWG - 4AWG

Configuration

Connector Type	THIN WALL TUBES/REELS
----------------	-----------------------

Dimensions

Width	0.375 in
Height	0.375 in
Length	3000 in
Dimensions	3000 in x 0.375 in x 0.375 in

General

Material	Polyvinyl chloride
UPC	781810265963

Logistics

Minimum Pack Quantity	4
Carton Quantity	1
Pallet Quantity	1

Product Assets

[Catalog \[English\]](#)