



HSB38FRFT, Heat Shrink Tubing, Thin, Flame Rtrdnt, Black

By Burndy
Catalog # [HSB38FRFT](#)



.38" ID Min (Expanded), .19" ID Max (Recovered), Black, Fire Retardant, Thin Wall, 25-Foot Reel

Features

- Heat Shrink Tubing, 0.38" ID Min (Exp), 0.19" ID Max (Rec)
- #8-#6, PVC, Fire Retardant
- Thin Wall, Black
- 250 Foot Reel

Specifications

Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	Yes

Current

Voltage Rating	600 V
----------------	-------

Dimensions

Height	0.375 in
Width	0.375 in
Package Height	0.000 in
Length	300 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimensions	300 in x 0.375 in x 0.375 in

General

Product Type	PVC Thin Wall Heat Shrink
UPC	781810033777

Logistics

Minimum Pack Quantity	50
-----------------------	----

Product Assets

[Catalog \[English\]](#)