



HSB38T300PF, Heat Shrink Tubing, Thin Wall, Black

By Burndy
Catalog # [HSB38T300PF](#)

.38" ID Min (Expanded), .19" ID Max (Recovered), Thin Wall, Black, Fire Retardant, 25-Foot Reel

Features

- Heat Shrink Tubing, 0.38" ID Min (Exp), 0.19" ID Max (Rec)
- #8-#6, Polyolefin, Thin Wall
- Black, 25 Foot Reel

Specifications

Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	No
Certification - CSA Approved	Yes

Conductor

Conductor Size	8AWG - 6AWG
Conductor Range	#8 AWG to #6 AWG

Configuration

Connector Type	THIN WALL REEL
----------------	----------------

Dimensions

Height	0.375 in
Width	0.375 in
Length	300 in
Dimensions	300 in x 0.375 in x 0.375 in

General

UPC	781810213667
Material	Cross-linked Polyolefin

Product Assets

[Catalog \[English\]](#)