



HSB38T48PF, Heat Shrink Tubing, Thin Wall, Black

By Burndy
Catalog # [HSB38T48PF](#)

.38" ID Min (Expanded), .19" ID Max (Recovered), Black, Fire Retardant, Thin Wall, 4-Foot Reel

Features

- Heat Shrink Tubing, 0.38" ID Min (Exp), 0.19" ID Max (Rec)
- #8-#6, Polyolefin
- Thin Wall, Black
- 4 Foot Reel

Specifications

Certification - CSA Approved	Yes
UL Listed	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	

Conductor

Conductor Range	#8 AWG to #6 AWG
Conductor Size	8AWG - 6AWG

Configuration

Connector Type	THIN WALL REEL
Dimensions	
Width	0.375 in
Height	0.375 in
Length	48 in
Dimensions	48 in x 0.375 in x 0.375 in

General

Material	Cross-linked Polyolefin
UPC	781810212608

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalog \[English\]](#)