



HSB38T6PF12, Heat Shrink Tubing, Thin Wall, Black

By Burndy
Catalog # [HSB38T6PF12](#)



.38" ID Min (Expanded), .19" ID Max (Recovered), Black, Fire Retardant, Thin Wall, 6" Lengths, 12 Pieces per package

Features

- Heat Shrink Tubing, 0.38" ID Min (Exp), 0.19" ID Max (Rec)
- #8-#6, Polyolefin, Thin Wall
- Black, Shrink Ratio 2:1

Specifications

Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	Yes

Conductor

Conductor Range	#8 AWG to #6 AWG
-----------------	------------------

Dimensions

Height	0.375 in
--------	----------

Width	0.375 in
Package Height	0.000 in
Length	6 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimensions	6 in x 0.375 in x 0.375 in

General

UPC	781810214541
Material	Polyolefin

Logistics

Minimum Pack Quantity	1
Carton Quantity	120

Product Assets

[Catalog \[English\]](#)