



HSBL14T48PF, Heat Shrink Tubing, Thin Wall, Blue

By Burndy
Catalog # [HSBL14T48PF](#)

.25" ID Min (Expanded), .125" ID Max (Recovered), Thin Wall, Blue, 4-Foot Reel

Features

- Heat Shrink Tubing, 0.25" ID Min (Exp), 0.125" ID Max (Rec)
- #14-#10, Polyolefin, Thin Wall, Blue
- Shrink Ratio 2:1
- 4 Foot Reel

Specifications

Certification - CSA Approved	Yes
UL Listed	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	

Conductor

Conductor Range	#14 AWG to #10 AWG
Conductor Size	14AWG - 10AWG

Configuration

Connector Type	THIN WALL REEL
----------------	----------------

Dimensions

Width	0.25 in
Height	0.25 in
Length	48 in
Dimensions	48 in x 0.25 in x 0.25 in

General

Material	Cross-linked Polyolefin
UPC	781810212585

Logistics

Minimum Pack Quantity	10
-----------------------	----

Product Assets

[Catalog \[English\]](#)