



HSBL316T300PF, Heat Shrink Tubing, Thin Wall, Blue

By Burndy
Catalog # [HSBL316T300PF](#)

.187" ID Min (Expanded), .093" ID Max (Recovered), Thin Wall, Blue, 25-Foot Reel

Features

- Heat Shrink Tubing, 0.187 ID Min (Exp), 0.093" ID Max (Rec)
- #18-#12, Polyolefin, Thin Wall, Blue
- Shrink Ratio 2:1
- 25 Foot Reel

Specifications

Certification - CSA Approved	Yes
UL Listed	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	

Conductor

Conductor Range	#18 AWG to #12 AWG
Conductor Size	18AWG - 12AWG

Configuration

Connector Type	THIN WALL REEL
----------------	----------------

Dimensions

Width	0.187 in
Height	0.187 in
Length	300 in
Dimensions	300 in x 0.187 in x 0.187 in

General

Material	Cross-linked Polyolefin
UPC	781810213575

Logistics

Minimum Pack Quantity	10
Carton Quantity	1
Pallet Quantity	1

Product Assets

[Catalog \[English\]](#)