



HSBL34T300PF, Heat Shrink Tubing, Thin Wall, Blue

By Burndy
Catalog # [HSBL34T300PF](#)

.75" ID Min (Expanded), .375" ID Max (Recovered), Thin Wall, Blue, 25-Foot Reel

Features

- Heat Shrink Tubing, 0.750" ID Min (Exp), 0.375" ID Max (Rec)
- #1-3/0, Polyolefin, Thin Wall, Blue
- Shrink Ratio 2:1
- 25 Foot Reel

Specifications

Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	Yes

Conductor

Conductor Size	1AWG - 3/0AWG
Conductor Range	#1 AWG to #3/0 AWG

Configuration

Connector Type	THIN WALL REEL
----------------	----------------

Dimensions

Height	0.75 in
Width	0.75 in
Length	300 in
Dimensions	300 in x 0.75 in x 0.75 in

General

UPC	781810213957
Material	Cross-linked Polyolefin

Logistics

Minimum Pack Quantity	10
Pallet Quantity	360
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)