



HSBL34T48PF, Heat Shrink Tubing, Thin Wall, Blue

By Burndy
Catalog # [HSBL34T48PF](#)

.75" ID Min (Expanded), .375" ID Max (Recovered), Thin Wall, Blue, 4-Foot Reel

Features

- Heat Shrink Tubing, 0.750" ID Min (Exp), 0.375" ID Max (Rec)
- #1-3/0, Polyolefin, Thin Wall, Blue
- Shrink Ratio 2:1
- 4 Foot Reel

Specifications

Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	Yes

Conductor

Conductor Size	1AWG - 3/0AWG
Conductor Range	#1 AWG to #3/0 AWG

Configuration

Connector Type	THIN WALL REEL
----------------	----------------

Dimensions

Package Height	0.000 in
Length	48 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Height	0.75 in
Width	0.75 in
Dimensions	48 in x 0.75 in x 0.75 in

General

UPC	781810212837
Material	Cross-linked Polyolefin

Logistics

Minimum Pack Quantity	1
Pallet Quantity	8448
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)