



HSBL38T48PF, Heat Shrink Tubing, Thin Wall, Blue

By Burndy
Catalog # [HSBL38T48PF](#)

.375" ID Min (Expanded), .187" ID Max (Recovered), Thin Wall, Blue, 4-Foot Reel

Features

- Heat Shrink Tubing, 0.375" ID Min (Exp), 0.187" ID Max (Rec)
- #8-#6, Polyolefin, Think Wall, Blue
- Shrink Ratio 2:1
- 4 Foot Reel

Specifications

Certification - CSA Approved	Yes
UL Listed	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	

Conductor

Conductor Range	#8 AWG to #6 AWG
Conductor Size	8AWG - 6AWG

Configuration

Connector Type	THIN WALL REEL
Dimensions	
Width	0.375 in
Height	0.375 in
Length	48 in
Dimensions	48 in x 0.375 in x 0.375 in
General	
Material	Cross-linked Polyolefin
UPC	781810212677
Logistics	
Minimum Pack Quantity	10
Carton Quantity	1
Pallet Quantity	1
Product Assets	
Catalog [English]	