



HSBLU112FR, Heat Shrink Tubing, Thin, Flame Rtrdnt, Blue

By Burndy
Catalog # [HSBLU112FR](#)



1.5" ID Min (Expanded), .75" ID Max (Recovered), Thin Wall, Blue, 25-Foot Reel

Features

- Flame Retardant
- Flexible Polyvinylchloride
- 2:1 Shrink Ratio
- 600 Volts

Specifications

Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	Yes

Conductor

Conductor Size	350kcmil - 750kcmil
----------------	---------------------

Configuration

Connector Type	THIN WALL TUBES/REELS
----------------	-----------------------

Current

Voltage Rating	600 V
----------------	-------

Dimensions

Height	1.5 in
Width	1.5 in
Package Height	0.000 in
Length	300 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimensions	300 in x 1.5 in x 1.5 in

General

Product Type	PVC Thin Wall Heat Shrink
UPC	781810265994
Material	Polyvinyl chloride

Logistics

Minimum Pack Quantity	8
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)