



HSBLU12FR, Heat Shrink Tubing PVC, Thin, Flame Rtrdnt, Blue

By Burndy
Catalog # [HSBLU12FR](#)



.50" ID Min (Expanded), .25" ID Max (Recovered), Thin Wall,
Flame Retardant, 50-Foot Reel

Features

- Flame Retardant
- Flexible Polyvinylchloride
- 2:1 Shrink Ratio
- 600 Volts

Specifications

Certification - CSA Approved	Yes
UL Listed	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	

Conductor

Conductor Range	#6 AWG to #4 AWG
Conductor Size	4AWG - 1AWG

Configuration

Connector Type	THIN WALL TUBES/REELS
----------------	-----------------------

Dimensions

Width	0.5 in
Height	0.5 in
Length	300 in
Dimensions	300 in x 0.5 in x 0.5 in

General

Material	Polyvinyl chloride
UPC	781810266014

Logistics

Minimum Pack Quantity	16
Carton Quantity	1
Pallet Quantity	1

Product Assets

[Catalog \[English\]](#)