



HSBLU34FR250, Heat Shrink Tubing, Thin, Flame Rtrdnt, Blue

By Burndy
Catalog # [HSBLU34FR250](#)



.75" ID Min (Expanded), .375" ID Max (Recovered), Thin Wall, Flame Retardant, Blue, 250-Foot Reel

Features

- Heat Shrink Tubing, 0.75" ID Min (Exp), 0.38" ID Max (Rec)
- 1/0-3/0, PVC, Fire Retardant
- Thin Wall, Blue
- Shrink Ratio 2:1
- 250 Foot Reel

Specifications

Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	Yes

Conductor

Conductor Size	1/0AWG - 3/0AWG
----------------	-----------------

Configuration

Connector Type	THIN WALL TUBES/REELS
----------------	-----------------------

Current

Voltage Rating	600 V
----------------	-------

Dimensions

Height	0.75 in
Width	0.75 in
Length	3000 in
Dimensions	3000 in x 0.75 in x 0.75 in

General

Product Type	PVC Thin Wall Heat Shrink
UPC	781810266090
Material	Polyvinyl chloride

Logistics

Minimum Pack Quantity	2
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)