



HSC100FR100, Heat Shrink Tubing PVC, Thin, FR, Clear

By Burndy
Catalog # [HSC100FR100](#)



1" ID Min (Expanded), .5" ID Max (Recovered), Thin Wall, Flame Retardant, Clear, 100-Foot Reel

Features

- PVC Clear Heat Shrink Tubing
- 4/0-300 Code, 1/0-4/0 Flex
- 600 V
- Fire Retardant

Application

Used on UL Recognized TO 600V

Specifications

Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Buy American Compliant	No
UL Listed	No
Certification - CSA Approved	Yes

Conductor

Conductor Size	4/0AWG - 300kcmil
Conductor Range	#1/0 AWG to #4/0 AWG

Configuration

Connector Type	CLEAR TUBES
----------------	-------------

Current

Voltage Rating	600 V
----------------	-------

Dimensions

Length	1200 in
Height	1 in
Width	1 in
Dimensions	1200 in x 1 in x 1 in

General

Color	Clear
Trade Name	VISI-SHRINK™
Sub Brand	VISISHRINK
Product Type	PVC Thin Wall Heat Shrink
UPC	781810266137
Type	HSC-FR, Fire Retardant
Material	Polyvinyl chloride

Logistics

Minimum Pack Quantity	1
Pallet Quantity	360
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)