



HSC112FRFT, Heat Shrink Tubing, Thin, FR, Clear

By Burndy
Catalog # [HSC112FRFT](#)



1.5" ID Min (Expanded), .75" ID Max (Recovered), Thin Wall, Clear, Flame Retardant, 25-Foot Reel

Features

- Heat Shrinkable Thin Wall Tube
- 600 V
- Shrink Ratio 2:1

Application

For Terminations And Splices

Specifications

Buy American Compliant	Contact Manufacturer
EU RoHS Indicator	Yes
Certification - ETL	No
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	Yes
UL Listed	No

Dimensions

Package Length	15 in
Package Width	11 in

Package Weight	2.3 lb.
Package Height	9 in
Length	300 in
Width	1.5 in
Height	1.5 in
Dimensions	300 in x 1.5 in x 1.5 in

General

Sub Brand	VISISHRINK
Type	HSC-FR, Thin Wall, Flexible, Fire Retardant
UPC	781810033739

Logistics

Minimum Pack Quantity	25
Carton Quantity	25
Pallet Quantity	1250

Product Assets

[Catalog \[English\]](#)