



HSC116T1200PF, Heat Shrink Tubing, Thin Wall, Clear

By Burndy
Catalog # [HSC116T1200PF](#)

.062" ID Min (Expanded), .032" ID Max (Recovered), Thin Wall, Clear, 100-Foot Reel

Features

- Heat Shrink Tubing, 0.062" ID Min (Exp), 0.032" ID Max (Rec)
- #18, Polyolefin, Thin Wall, Blue
- Shrink Ratio 2:1
- 100 Foot Reel

Specifications

Certification - CSA Approved	Yes
UL Listed	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM

Conductor

Conductor Range	#18 AWG
-----------------	---------

Dimensions

Width	0.062 in
Height	0.062 in
Length	1200 in
Dimensions	1200 in x 0.062 in x 0.062 in

General

Material	POLYOLEFIN
UPC	781810271612
Color	Clear

Logistics

Minimum Pack Quantity	10
-----------------------	----

Product Assets

[Catalog \[English\]](#)