



HSC12FR, Heat Shrink Tubing, Thin, Flame Rtrdnt, Clear

By Burndy
Catalog # [HSC12FR](#)



.50" ID Min (Expanded), .25" ID Max (Recovered), Thin Wall, Fire Retardant, Clear, 50-Foot Reel

Features

- Flame Retardant
- Flexible Polyvinylchloride
- 2:1 Shrink Ratio
- 600 Volts

Application

For Terminations And Splices

Specifications

Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	Yes

Conductor

Conductor Size	4AWG - 1AWG
Conductor Range	#6 AWG to #4 AWG

Configuration

Connector Type	CLEAR TUBES
----------------	-------------

Current

Voltage Rating	600 V
----------------	-------

Dimensions

Height	0.5 in
Width	0.5 in
Length	600 in
Dimensions	600 in x 0.5 in x 0.5 in

General

Product Type	PVC Thin Wall Heat Shrink
Color	Clear
UPC	781810266175
Trade Name	VISI-SHRINK™
Type	HSC-FR, Thin Wall, Flexible, Fire Retardant
Sub Brand	VISISHRINK
Material	Polyvinyl chloride

Logistics

Pallet Quantity	128
Carton Quantity	16

Product Assets

[Catalog \[English\]](#)